



Main

Range	PratiKa
Product or component type	Wander socket
Device short name	PratiKa socket
Plug, socket category	Low voltage
Poles description	3P + N + E
Network type	AC
Outlet standard	Industrial

Complementary

Plug, socket, control station shape	Straight
[In] rated current	63 A
[Ue] rated operational voltage	380...415 V
Network frequency	50/60 Hz
Ground lug clockwise position	6 h
Plug, socket material	Housing: self-extinguishing engineering polymer
Contacts material	Pins: stainless steel Sleeves: nickel plated brass Springs: stainless steel
Connections - terminals	Captive screws
Cable cross section	6...25 mm ²
Cable outer diameter	17...31 mm
Cable entry	Cable gland
Thread type	Pg 36
Net weight	0.783 kg
Height	110 mm
Width	110 mm
Depth	265 mm
Colour	Grey (RAL 7035)
Voltage colour	Red

Environment

Standards	IEC 60309-2 IEC 60309-1
IP degree of protection	IP67 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 62262
Fire resistance	850 °C conforming to IEC 60695-2-1
Relative humidity	50 % at 40 °C 70 % at 30 °C 90 % at 20 °C
Ambient air temperature for operation	35 °C (86400 s) -25...40 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	794 g
Package 1 Height	10.8 cm
Package 1 width	10.9 cm
Package 1 Length	27.6 cm
Unit Type of Package 2	S03
Number of Units in Package 2	10
Package 2 Weight	8.427 kg
Package 2 Height	30 cm
Package 2 width	30 cm
Package 2 Length	40 cm

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile