


MODULE MOUSSE M4 1/4" – 3/8" – 1/2". CLIQUET / DOUILLE OGV GRIP

MODM.XXL1GRPPF



1/4"		<ul style="list-style-type: none">  ED 101T - 102T - 103T  EH 103 - 104 - 105 - 106 - 107  EP 101T - 102T - 103T  ES 134.5T - 136.5T - 148T  EXR 110 - 115 - 120 - 125 - 127 - 130 - 140
		<ul style="list-style-type: none">  JX.T T45 - T50 - T55
1/4"		R.216
		R.236CA
		R.235

							
1/4'	R.GRP. 5,5-6-7-8-9-10-11-12-13-14 mm	R.PE360 RL.161 R.180	EF.R180 - 100 mm R.209 - 55 mm R.210 - 100 mm	R.229A	-	R.240A	ECR
	R.LA 6-7-8-9 mm						
1/2'	S.GRP 10 -11-12-13-14-15-16-17-18-19-21-22-24-27-30-32 mm	SXL.161	S.208S - 75 mm S.210S - 130 mm S.215S - 250 mm	S.120A	S.230	S.240A	
	S.HLA 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 21 - 22 - 23 - 24 - 27 mm						
	S. 10-11-12-13-14-15-16-17-18-19-21-22-23-24-27-30-32 mm						
3/8"	J.H 8-9-10-11-12-13-14- 15-16-17-18 -19-21-22 mm	JL.161	J.210S - 125 mm J.215 - 250 mm	-	J.230	J.240A	
	J.HLA : 8 - 9 -10 - 16 - 17 - 18 - 19 - 21 - 22 mm						
	J. 8-9-10-11-12-13-14-15-16-17-18-19-21-22 mm						
1/2" 3/8" 1/4"		D.169					