

Features

- Cutter – All-purpose tool that can be used as shears and pliers.
- For cutting electrical cables Ø max 10 mm (000 awg)
- Steel thickness 3mm.
- Anti-reflection phosphating surface treatment
- Anti-slip bi-material dolphin handle with light and comfortable grip
- Made in Italy

RS PRO Cable cutting pliers

RS Stock No.: 0616312



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

RS PRO Cable Cutting Pliers.

RS PRO Cutter – All-purpose tool that can be used as shears or pliers.

Ideal for cutting electrical cables Ø max 10 mm (000 awg). Steel thickness 3mm. Tool is equipped with a return spring designed to have a constant force, thus reducing operator effort.

Made with high carbon steel and undergo a controlled atmosphere heat treatment. The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.

The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator.

General Specifications

Materials Cut	Electrical cables Ø max 10 mm (000 awg)
No Sparking	No
Overall Length	170mm
VDE/1000V Approved	No
Height Safe	No
ESD Safe	No
Material	High Carbon Steel
Maximum Cutting Capacity	Ø max 10 mm (000 awg)

Approvals

Declarations	REACH DoC
--------------	-----------

