




Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Tab**

Connector & Housing Type: **Tab Housing**

Number of Positions: **5**

Terminal Orientation: **Straight**

UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Tab Housing

Configuration Features

Number of Positions	5
---------------------	---

Body Features

Connector & Keying Code	C
Primary Product Color	Natural

Contact Features

Terminal Type	Tab
Terminal Orientation	Straight
Contact Mating Retention	With

Mechanical Attachment

Mating Alignment Type	Polarization
-----------------------	--------------



Mating Retention Type	Locking Lance
-----------------------	---------------

Mating Alignment	With
------------------	------

Connector Mounting Type	Panel Mount
-------------------------	-------------

Housing Features

Housing Material	Polyamide
------------------	-----------

Centerline (Pitch)	5 mm [.196 in]
--------------------	----------------

Dimensions

Product Length	30.5 mm [1.2 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-25 – 105 °C [-13 – 221 °F]
-----------------------------	-----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	200
--------------------	-----

Packaging Method	Carton
------------------	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
--	---

Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous

materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 6-927742-6
6 POS FASTIN/ON HOUSING PANEL MOUNT



TE Part # 293161-1
5 POS. FASTIN-FASTON* TAB HSG, RAST5




TE Part # 1955416-1
3 POS. FASTIN-FASTON CONNECTOR TAB HOUSI




TE Part # 964492-2
2 POS FASTIN/ON HOUSING PANEL MOUNT


Also in the Series | **RAST 5 IDC Connectors**



Card Edge Connector Housings(19)



Crimp Terminal Housings(39)




Insertion & Extraction Tools(1)




PCB Headers & Receptacles(418)



Rectangular Power Connectors(658)



Standard Edge Connectors(31)



Wire-to-Board Headers & Receptacles (418)

Customers Also Bought



TE Part #175218-2
DYNAMIC REC CONTACT L L/P



TE Part #175363-1
DYNAMIC D-3500 REC HSG 4P



TE Part #350218-1
UMNL PIN 20-14 .0126PTPBR



TE Part #350536-1
UMNL SOK 20-14 .0126 PTPBR



TE Part #2-520337-2
ULTRA-FAST 187 ASY REC 22-18 TPBR



TE Part #9-927742-2
2POS FASTIN FASTON HOUSING



TE Part #2150382-2
OCEAN_2.0_APPLICATOR-E-110F1800-SEA



TE Part #CAT-M9194-CH8172
MULTILOCK, CONNECTOR HOUSING



Documents

Product Drawings

[5POS. FASTIN-FASTON* TAB HSG, RAST5](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_9-1241857-5_D.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_9-1241857-5_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-1241857-5_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English

Product Specifications

[Product Specification](#)

English

Agency Approvals

[UL Report](#)

English