Sicad S.p.A.
Via Caduti della Liberazione, 57
21040 Uboldo (VA) – Italia
Tel: +39 02 964121 Fax: +39 02 96412294
Web: www.eurocel.it

PRODUCT INFORMATION
EUROCEL SF 4342AR

DESCRIPTION

Single sided tape coated on orange soft PVC, easy unwinding.

PRODUCT DATA

Backing	Soft PVC, treated on the back; orange
Adhesive	Dry natural rubber and resins, solvent based

	Unit	Value	Method
Total thickness	mm	0.124	PSTC 133
Adhesion to steel	N/25mm	3	PSTC 101
Tensile strength MD	N/25mm	62	PSTC 131
Elongation at break	%	240	PSTC 131
Temp. Resistance	°C	60°C	=

APPLICATION

Single sided self adhesive tape designed for the building industry as a masking and protection tape for all rough casting and façade works. It is also used for all repair and identification purposes. Very easy to unwind.

Features	Benefits
Dry natural and resins rubber, solvent based	✓ Very high adhesion and tack ✓ Removal without adhesive residue ✓ Suitable on all substrates
Soft PVC backing	✓ Very easy to unwind ✓ High conformability ✓ Hand tearable ✓ Stable in dimension ✓ Weather resistant

CONDITIONS OF USE AND CONFORMITY

Product shelf life and storage: 12 months; suggested storage temperature shall range from 15°C to 25°C with max. relative humidity of 65%. Material shall be stored away from heat sources and possibly kept in original package, avoiding light exposure as well. When temperatures are lower than suggested, it is always required to recondition the tape at normal temperature before use. This information is given to the best of Sicad's knowledge. Values are typical and do not constitute a specification. Customers are required to do their own testing under their working condition for their intended application. Any liability arising in respect of our products will be limited to the value of those products charged to the customer excluding any consequential loss.

Società Italiana Cellophane Adesivo
P.I. e C.F. IT 00220060123
Iscrizione R.E.A. Varese n. 129175
Reg. Imprese Varese n. 00220060123
Capitale Sociale € 15.000.000 i.v.