


## Technical data sheet

### Article number:

**111-01815**

**T18R**



<b>Product Group</b>	Cable ties polyamide 6.6 standard
<b>Product Family</b>	T-Series in PA66 coloured
<b>Material</b>	Polyamide 6.6 (PA66)
<b>Colour</b>	Green (GN)

<b>Bundle Ø max.</b>	22.0 mm
<b>Bundle Ø min.</b>	1.5 mm
<b>Flammability</b>	UL 94 V2
<b>Halogen-free</b>	Yes
<b>Height (H)</b>	3.7 mm
<b>Length (L)</b>	101.6 mm
<b>Min.Tensile Strength</b>	80 N
<b>Operating Temperature</b>	-40 °C to +85 °C
<b>Package Content</b>	100 pcs.
<b>Package Content packed in</b>	bag
<b>Releasable Closure (Yes/No)</b>	No
<b>Specifications</b>	BV 03856/H0 BV, IEC 62275:2006
<b>Thickness (T)</b>	1.0 mm
<b>Toothing (Serration)</b>	Inside Serrated
<b>UV-Stabilised</b>	No
<b>Variant</b>	Inside Serrated
<b>Width (W)</b>	2.5 mm

**HF** ✓ **RoHS** ✓

