



All AMPOWER Terminal Without Stud Hole (0)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46749-2
HYP8 AMPOWER 3/0AWG DIE SET



TE Part # 1583097-1
DIE ASSY,AMPOWER,3/0

Customers Also Bought



TE Part #770987-1
MINI UMNL PIN 22-18AWG SN LP



TE Part #1676322-2
RN 0805 3K01 0.1% 10PPM 1KRL



TE Part #710032-6
XCT 6-8



TE Part #CAT-HST-RNF3000
RNF-3000 Heat Shrink Tubing




TE Part #NB08012001
HTAT-4/1-0-STK



TE Part #34318
SPLICE, SOLIS, PARA, 8



TE Part #9-1879028-1
RN 0805 464K 0.1% 10PPM 1K RL



TE Part #5069804009
CGPT-1.6/0.8-0-SP



TE Part #NB11652001
ATUM-6/2-0-STK

Documents

Product Drawings
TERMINAL,AMPOWER 3/0 0
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_325508_Z.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_325508_Z.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_325508_Z.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[AMPOWER Terminals and Splices Flyer](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[UL Report](#)

English