

Specification



Physical Specifications

Dimensions	80.0 (L) x 126.0 (W) x 15.8(D) mm
Power	DC 5V (USB self powered)
Interface	USB 2.0 / 1.1
Data Transfer	MAX 480Mbps (USB2.0)
Color	Black / White

HDD Specifications

Capacity	160 / 250 / 320 / 500GB
Buffer size	8MB
Life cycle	600,000 cycles
RPM	5,400 rpm
File format	NTFS

System Requirements

OS	Windows 98 / ME / 2000 / XP / Vista Mac OS 10.0 or later
PC	CPU : Intel Pentium II 350Mhz above RAM : 60MB above HDD : 2GB free space

ETC

Accessory	External HDD, USB cable, Quick guide, CD
Warranty	2 Years
Utility	Back-up S/W, Windows 98 driver
Certification	CE / FCC