

# Thrust ball bearings, single direction



Principal dimensions			Basic load ratings		Fatigue load limit $P_u$	Minimum load factor $A$	Speed ratings		Mass kg	Designation
d	D	H	dynamic	static			Reference speed	Limiting speed		
mm			kN		kN	-	r/min			-
25	47	15	27,6	55	2,04	0,015	5300	7500	0,11	51205

