



Part Number : [2064611800](#)

Product Description : Micro-Fit+ Receptacle Housing, Dual Row, 18 Circuits, UL 94V-0, Glow-Wire Capable, Black

Series Number : 206461

Status : Active

Product Category : Connector Housings



Documents & Resources

Drawings

[2064611800_sd.pdf](#)

[2064610000-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2064600001-AS-000.pdf](#)

[2064600000-PS-000.pdf](#)

[2159530000-PS-000.pdf](#)


[2064600000-TS-000.pdf](#)

[2064600001-TS-000.pdf](#)

[2159530000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	206461
Description	Micro-Fit+ Receptacle Housing, Dual Row, 18 Circuits, UL 94V-0, Glow-Wire Capable, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Name	Micro-Fit+
UPC	191130004751

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	18
--------------------	----

Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.813/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit+ Vertical, Dual Row, Through Hole Headers	<u>206832</u>
Micro-Fit+ Right-Angle, Dual Row, Through Hole Headers	<u>212528</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>

Use with Part(s)

Description	Part Number
Micro-Fit+ Female Crimp Terminals	<u>206460</u>
Micro-Fit+ Terminal Position Assurance (TPA) Retainers	<u>206462</u>