

DCLE34035B-XJ

3x360° XR 18V multi-line laser level - green beams - remote controlled

5035048834664



Product Description:

Working range (diameter) (m): 70 - 100 with cell
Remote control range: 100 m
Accuracy: +/- 3 mm to 10 m
Tripod thread: 3/8" - Magnetic angle-clamp holder
Water and dust protection: IP54

Product features and benefits:

- **MAKES YOUR JOB EASIER!** Remote control with a range of 100 m to **PRECISELY** adjust the laser beams horizontally (up to 120°) AND vertically (approx. 9 cm).
- **VERY EFFICIENT:** new very high visibility 3x360° green beam diodes. 80 m / 100 m with detection cell.
- **VERY PRECISE:** possibility to manually adjust the laser left/right/up/down. Short press to move a notch. Long press to increase the speed by 3 notches every 2 Seconds.
- **PRACTICAL:** indicators to check the battery charge level and the use of the remote control.
- **ADAPTS TO THE CONDITIONS OF THE CONSTRUCTION SITE:** 3 levels of light intensity. Choice of the number of beams.
- **ATTACHES ANYWHERE:** on 5/8" tripod - On a magnetic stand, with clamp/screw for edge angle. Also Arises directly on the ground (very stable).
- **POSSIBILITY OF MAKING CREEPERS** (with slope adapter) with 3-position button: manual slope / automatic leveling / compensator lock.

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Laser (x1) Remote
- Control (x1) Wall
- Mount (x1)
- Target (x1) TSTAK
- Box (x1)

Specifications techniques :

- [Imperial] Battery Capacity: 2 Ah

