

END75N



Length (mm)	Width (mm)	Height (mm)	Diameter cable grooves (mm)	Weight (kg)
250	300	75	-	4.0

Made of: Vulcanized virgin rubber

Colors: Black

Range: SIGN

Custom: 4016999790

EAN: 3321369984822

Specifications:

- Ending part for heavy duty speed bump for EASYSPEED75NJ
- Height of 75mm to reduce speed up to 10/15 km/h
- Can support up to 40 tons
- Resist to grease, base and acids
- Avoid over long contact with hydrocarbons
- Supplied with asphalt fixation and cap, concrete fixation as option
- H link sold separately as option