

PRODUCT-DETAILS

# TC376

## STAND-OFF BRKT MTG BASE 1.75IN NAT



### General Information

Extended Product Type	TC376
Product ID	7TAG009910R0086
EAN	5414363058793
Catalog Description	STAND-OFF BRKT MTG BASE 1.75IN NAT
Long Description	Stand-Off Brackets Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 44.45mm (1.75 Inches), Width of 17.5mm (0.69 Inches), Height of 17.0mm (0.67 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.8mm (0.189 Inches)

### Ordering

EAN	5414363058793
UPC	786210826837

### Container Information

Package Level 1 Units	100 piece
Package Level 2 Units	1000 piece
Package Level 2 Width	8.5 in 216 mm
Package Level 2 Height	7.6 in 193 mm
Package Level 2 Depth / Length	16.3 in 414 mm

## Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19680823
Material	Nylon/Polyamide 6.6
Mounting Type	Screw
Number of Batteries	0
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Stand-Off Brackets
Special Functions	These brackets permit bundles to be mounted on either side. They also serve as means to raise bundles off the surface.

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TC376
Declaration of Conformity - CE	9AKK107492A9840
Instructions and Manuals	TC376
REACH Declaration	9AKK107992A8796
RoHS Information	9AKK107992A8808

## Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

