

# PRODUCT SHEET

## 236-...G

### Polished chrome-plated flat nose pliers


Forged in steel with chrome-vanadium.

Inner of the nose grooved for a better tightening.

236-26GE pattern: nose frayed for a precision tightening.

Bimaterial branches.

Polish chromed finishing.



Normes : NF ISO 5745

#### HIGH FREQUENCY HARDENING

reference	E mm	e1 mm	e2 mm	L1 mm	L mm	L''	Weight g
236-16G	6		8	50	160		140
236-20G	5		8	50	200		160