

COAST

XPH34R MULTI-PURPOSE HEAD TORCH



DUAL POWER

ZITHION-X™ Rechargeable – Also works with CR123 Lithium or Alkaline batteries



2000
LUMENS BRIGHT

DUST RESISTANT WEATHER PROOF
IP54

POWER SOURCES:
LI ION OR LITHIUM OR ALKALINE

COAST TRUSTED TOUGH™

FIVE YEAR WARRANTY

XPH34R



COAST Introduces its Most Powerful Ever 2000 Lumens Head torch in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The COAST XPH34R rechargeable head torch gives users amazing versatility and delivers COAST's most powerful brightness. The torch has a maximum lumen output of 2000 on Turbo Mode, and 1000 lumens on High.

The XPH34R features a compact, dust-resistant aluminum body that rolls in its bracket for dynamic directional lighting. You can pull the torch out of the bracket to use as a handheld; there is also a magnet on the battery cap which allows you to affix the torch to metal surfaces.

Powered by a COAST ZITHION-X™ rechargeable battery with a real-time battery life indicator, the torch features a twist focus, and four light output options. The light features COAST's Dual Power™ technology, meaning the torch is also compatible with two CR123 batteries (sold separately) or three AAA alkaline batteries (sold separately).

- 2000 lumens on Turbo Mode with rechargeable battery cell
- ZITHION-X™ rechargeable battery (included), 2 x CR123 (sold separately), or 3 x AAA batteries (sold separately)

