

Yale

Iron Padlocks

With over 185 years of manufacturing expertise, the Yale Iron Padlocks have been built with you in mind.

Our hard-wearing iron padlocks are available in silver and black, and come in 5 different sizes to meet your security needs. These padlocks can secure everything from indoor items like your gym locker or toolbox, to securing your outdoor spaces such as ladders, garages and gates.

Application & Certification



Toolbox



Locker



Ladder



Gate



Shed



Garage



EN Certified

Features

- Iron construction.
- Hardened shackle to prevent cutting.
- Independently tested to EN12320 and EN1670.
- Designed for durability with 10,000 open/close cycles performance.
- Available in keyed alike multipacks
- Blister or boxed packaging available.

Trusted every day



Description	32mm Iron Padlock	32mm Iron Padlock Long Shackle	38mm Iron Padlock	38mm Iron Padlock Long Shackle
Black Padlock Part no.	Y111B/32/116/1	Y111B/32/148/1	Y111B/38/121/1	Y111B/38/156/1
Silver Padlock Part no.	Y111S/32/116/1	-	Y111S/38/121/1	-
Locking points	Double Locking	Double Locking	Double Locking	Double Locking
Body material	Iron	Iron	Iron	Iron
Shackle material	Hardened steel	Hardened Steel	Hardened steel	Hardened steel
Vertical shackle clearance	16.5mm	49mm	21.3mm	56.2mm
Horizontal shackle clearance	16.7mm	16.7mm	19.7mm	19.7mm
Weight with keys	82g	93.6g	126.7g	146.9g
Dimensions (mm)	W: 32 H: 30 D: 13.5 Ø: 5.3	W: 32 H: 30 D: 13.5 Ø: 5.3	W: 38 H: 34 D: 15 Ø: 6.3	W: 38 H: 34 D: 15 Ø: 6.3
Corrosion resistance	96 Hours	96 Hours	96 Hours	96 Hours
Keys	3 Keys	3 Keys	3 Keys	3 Keys
Pins	5 Pins	5 Pins	5 Pins	5 Pins
CEN rating	1	1	1	1
Multi-pack code	Y111B/32/116/2 (for pk2)	-	Y111B/38/121/4 (for pk4)	-



Description	50mm Iron Padlock	50mm Iron Padlock Long Shackle	60mm Iron Padlock	60mm Iron Padlock Long Shackle	75mm Iron Padlock
Black Padlock Part no.	Y111B/50/125/1	Y111B/50/160/1	Y111B/60/132/1	Y111B/60/172/1	Y111B/75/140/1
Silver Padlock Part no.	Y111S/50/125/1	-	Y111S/60/132/1	Y111S/60/172/1	Y111S/75/140/1
Locking points	Double Locking	Double Locking	Double Locking	Double Locking	Double Locking
Body material	Iron	Iron	Iron	Iron	Iron
Shackle material	Hardened steel	Hardened steel	Hardened steel	Hardened steel	Hardened steel
Vertical shackle clearance	25mm	60mm	32.3mm	72.3mm	39mm
Horizontal shackle clearance	25mm	25mm	32.5mm	32.5mm	40mm
Weight with keys	251.8g	286.7g	434.3g	485.7g	660.9g
Dimensions (mm)	W: 50 H: 41 D: 18 Ø: 9	W: 50 H: 41 D: 18 Ø: 9	W: 63 H: 50 D: 21 Ø: 10.5	W: 63 H: 50 D: 21 Ø: 10.5	W: 75 H: 58 D: 24 Ø: 12
Corrosion resistance	96 Hours	96 Hours	96 Hours	96 Hours	96 Hours
Keys	3 Keys	3 Keys	3 Keys	3 Keys	3 Keys
Pins	5 Pins	5 Pins	5 Pins	5 Pins	5 Pins
CEN rating	1	1	2	2	2
Multi-pack code	Y111B/50/125/4 (for pk4)	-	-	-	-