

CONTACTUM



Make the switch

2 Gang 13A DP RCD Latching Socket (2 Gang Plate) + Back Box - Metalclad, White Insert

Stock code: CLA4900M



General

Face plate finish:	metal
Insert colour:	white
Number of outlets:	2
Rocker finish:	white moulded
Switched:	Yes
With RCD:	Yes

Technical

Associated standards:	BS 7288
Ambient operating temperature:	-5 to 40°C (24hour average not exceeding 25°C)
Base material:	Thermoset
Face plate material:	steel
Fault current rating (mA):	30
Fixing screws:	2 x M3.5
IP rating:	IP2X
Maximum installation altitude:	2000m
Minimum switch contact gap:	3 mm
Nature of supply:	AC
Operational testing:	30000
Rated current:	13A
Rated frequency:	50-60Hz
Rated voltage:	220-250V
Switched poles:	2 pole
Terminal capacity:	3 x 2.5mm 3 x 4.0mm 2 x 6.0mm

Technical: +44 (0) 208 208 7414 Sales: +44 (0) 208 208 7419 E-mail: sales@contactum.co.uk