



Technical Data Sheet

DALO[®] Marker

Industrial Steel Ball Tip Paint Marker

FEATURES

- Heavy duty, industrial paint marker that writes on almost any surface.
- Writes through oil and grease without losing legibility or brightness.
- Makes permanent bright marks on metal, rubber, plastic, glass, concrete, leather, stone, wood, vinyl and more.
- Marks in extreme conditions, even writes under water and on rusty surfaces.
- Ergonomically correct marker that enables you to mark at all angles, even upside down.
- Markers can be used to permanently identify inventory, assemblies, tools, work in progress or finished products while resisting most work related abuses or compounds.
- Heavy duty aluminum body with large paint capacity.
- Paint flow is controlled by the pressure bulb at the end of the barrel.
- Stainless steel ball tips won't wear out on rough or rusty surfaces.
- Available in 2 tips sizes – Medium and Broad.

MATERIALS COMPATIBILITY

- Safe on most surfaces.
- Surface tests should be run to determine compatibility prior to use.

HEALTH AND SAFETY

- Combustible liquid and vapor. Keep away from heat, sparks and flame. Use only with adequate ventilation. Avoid contact with skin and eyes.
- Refer to MSDS (Material Safety Data Sheet) for complete information on health and safety. Visit our website at www.dykem.com to obtain an MSDS.

DIRECTIONS FOR USE

- To start flow press rubber bulb to pressurize
- Depress steel ball tip to start flow.
- Wipe tip clean before storing

AVAILABLE IN:

<u>Color</u>	<u>Medium Tip</u>	<u>Broad Tip</u>
Black	26033	26034
Blue	26013	26014
Green	26043	26044
Orange	26103	26104
Red	26023	26024
White	26083	26084
Yellow	26063	26064

PHYSICAL PROPERTIES

Appearance:	Varies
Odor:	Aromatic
Specific gravity:	>1
VOC level:	21% - 36% by weight
Flash point:	108°F
Dry Time*:	25-35 minutes

* Note: Drying time may vary depending on film thickness.