

Metric Size - TU TU0805S1-100

Datasheet

General series information

- Applicable tubing O.D.: Ø 2 to Ø 16 mm
- Operating temperature: -20 to 60 °C
- 29 colour variations.

Standard specifications

Size	0805 (O.D. Ø8 I.D. Ø5)
Color	S1 (Silver)
Roll Length	100 m
Reel Length	None
Suffix	None
Pressure medium	Air, Water
Maximum ambient temperature	60 °C / 40 °C for Water
Minimum ambient temperature	-20 °C (with no freezing) / 0 °C for Water
Number of pneumatic connections	2 pcs.
Max. operating pressure at 20 °C	0.8 MPa
Weight	3.500 Kg

Additional information

Catalogue

[TU-29COLOR-A_EU.pdf](#)