

Datasheet

Name: **All-round luminaire**
 2x26W TC-DE/G24q-3 220-240V 0/50-60Hz

Type: 796-1867

Description: Electronic ballast.



Technical specification

Colour:	White
Material:	Polycarbonate
Electronic control gear:	x
Enclosure class:	IP44
Impact resistance (J):	IK05
Light source:	2xTC-DE 26W / G24q-3
Operating frequency (Hz):	0/50-60 Hz
Rated voltage (V):	220-240 V
Weight (kg):	1,750 kg
Dimensions (mm), diameter x height:	400x122 mm
Recessing dimensions:	Ø380x80 mm

