

PRODUCT-DETAILS

# TY28MX-RW

## TY28MX FOR RAILWAY



### General Information

Extended Product Type	TY28MX-RW
Product ID	7TCG009210R0086
EAN	5415022180206
Catalog Description	TY28MX FOR RAILWAY
Long Description	Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant for Exterior Applications, Length of 361mm (14.2 Inches), Width of 4.8mm (0.19 Inches), Tensile Strength Rating of 50 Newtons (222 Pounds), 1000 Bulk Pack

### Ordering

EAN	5415022180206
UPC	786209717054

### Dimensions

Product Net Width	0.19 in 4.82 mm
Product Net Depth / Length	14.2 in 360.68 mm

### Container Information

Package Level 1 Units	1000 piece
-----------------------	------------

Package Level 1 Width	13.75 in 349 mm
Package Level 1 Height	1.96 in 50 mm
Package Level 1 Depth / Length	19.65 in 499 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	10.21 in 259 mm
Package Level 2 Height	14.14 in 359 mm
Package Level 2 Depth / Length	19.65 in 499 mm

## Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

## Additional Information

Brand / Label	Ty-Rap
Color	Black
Effective Date	20130730
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	OTHER ARTICLES OF PLASTIC

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000518
Instructions and Manuals	TY28MX-RW
REACH Declaration	9AKK107992A4002
RoHS Information	9AKK107991A8072

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

