










Lever Action Crimping Pliers - Technical Details

Article-No.	Length mm	EAN-Code	Head	Handles	Range of Application	Capacity	
		4003773-				mm ²	
97 52 02	250	025436	burnished	plastic-coated	 For non insulated terminals and connectors	0,25-2,5 AWG 23-14	550
97 52 03	250	025443	burnished	plastic-coated	 For non insulated terminals and connectors	4,0-10,0 AWG 12-7	550
97 52 04	250	025450	burnished	plastic-coated	 For non-insulated open plug type connectors 2,8+4,8 mm	0,1-1,5 AWG 27-15	550
97 52 05	250	025467	burnished	plastic-coated	 For non-insulated open plug-type connectors 4,8+6,3 mm	0,5-6,0 AWG 20-10	550
97 52 06	250	025474	burnished	plastic-coated	 For insulated terminals and connectors	0,5-6,0 AWG 20-10	550
97 52 08	250	025481	burnished	plastic-coated	 cable connectors (ferrules)	0,5-6,0	550
97 52 09	250	025498	burnished	plastic-coated	 cable connectors (ferrules)	10,0-25,0	550
97 52 10	250	023678	burnished	plastic-coated	 For coax connectors BNC-TNC for cables RG 58/59/62/71		550
97 59 04		026969	positioning aid for Art.-No. 97 52 04				
97 59 05		026983	positioning aid for Art.-No. 97 52 05				



97 52 03



97 52 06



97 52 09