





中文		⚠ 危险	触摸带电部件有生命危险 该设备 / 部件带有危险电压。触摸带电部件可造成严重身体伤害甚至死亡。电源电压断开后，设备内的危险电压仍然存在最长 2 分钟。只能由有资质的专业人员进行安装、调试和维护。请遵守操作说明和相关软起动器手册中的说明。
		⚠ DANGER	Danger to life when live parts are touched This device/part carries dangerous voltages. Death or serious injury will result if you touch live parts. The dangerous voltage is still present inside the device for up to 2 minutes after the supply voltages have been disconnected. Installation, commissioning and maintenance by qualified technicians only. Read the information provided in the operating instructions and manuals of the corresponding Soft Starter.


3RW511.-.....
3RW512.-.....
3RW513.-.....
3RW511.-.....-0S*
3RW512.-.....-0S*
3RW513.-.....-0S*



Position	Article Number (Spare Part)	Article Number (Soft Starter)
1	3RW5950-0GL20 3RW5950-0GL40	3RW51.-..... 3RW51.-.....-0S*
2	3RW5980-1TR00	3RW51.-.....
3	3RW5980-0HS00	3RW51.-.....-0S*
4	3UF7931-0AA00-0	3RW51.-.....-0S*
5	3RW5910-1UA10	3RW51.-.....
6	3RW5913-0PY04	3RW511.-..... 3RW512.-..... 3RW513.-.....
7	3RW5912-0TB00	3RW511.-..... 3RW512.-.....
8	3RW5982-0TB00	3RW511.-..... 3RW512.-.....
9	3RW5912-0SA04 3RW5912-0SB04 3RW5912-0SC04 3RW5912-0SD04 3RW5912-0SE04 3RW5952-0SF04 3RW5952-0SH04 3RW5952-0SJ04 3RW5953-0SL04 3RW5953-0SM04	3RW5113-..... (3x) 3RW5114-..... (3x) 3RW5115-..... (3x) 3RW5116-..... (3x) 3RW5117-..... (3x) 3RW5124-..... (3x) 3RW5125-..... 3RW5126-..... (3x) 3RW5127-..... (3x) 3RW5134-..... 3RW5135-..... (3x) 3RW5136-..... (3x)
10	3RW5953-0GB00	3RW511.-..... 3RW512.-..... 3RW513.-.....
11	3RW5983-0FF00	3RW5126-..... 3RW5127-..... 3RW513.-..... (2x)

Position	Assembly	Screws	Tightening torque
A	2 - a	3,5 mm x 19	140 Ncm
B	b - c	M4 x 12	230 Ncm
C	b - 6	M5 x 28	350 Ncm
C	b - 6	M6 x 29	350 Ncm
C	b - 6	M8 x 30	900 Ncm
D	a - 7	3,5 mm x 19	140 Ncm
E	c - 6	M5 x 10	350 Ncm
E	c - 6	M6 x 10	350 Ncm
E	c - 6	M8 x 12	900 Ncm
F	6 - d	M5 x 16	350 Ncm

3RW514.-.....
3RW514.-.....-0S*



Position	Article Number (Spare Part)	Article Number (Soft Starter)
1	3RW5950-0GL20	3RW51.-.....
	3RW5950-0GL40	3RW51.-.....-0S*
2	3RW5980-1TR00	3RW51.-.....
3	3RW5980-0HS00	3RW51.-.....-0S*
4	3UF7931-0AA00-0	3RW51.-.....-0S*
5	3RW5910-1UA10	3RW51.-.....
6	3RW5954-0GF00	3RW514.-.....
7	3RW5914-0PY04	3RW514.-.....
8	3RW5924-0SN05	3RW5143-..... (3x)
	3RW5924-0SQ05	3RW5144-..... 3RW5145-..... (3x)
	3RW5924-0SS05	3RW5146-..... 3RW5147-..... (3x)
	3RW5924-0ST05	3RW5148-..... (3x)
9	3RW5954-0GB00	3RW514.-.....
10	3RW5984-0FF00	3RW514.-.....

Position	Assembly	Screw	Tightening torque
A	2 - 3	3,5 mm x 19	140 Ncm
B	3 - a	3,5 mm x 19	140 Ncm
C	a - 6	5 mm x 40	350 Ncm
D	b - 5	M6 x 25	1200 Ncm
E	c - 5	M4 x 12	220 Ncm