



WHP3000, 1200 W

Item No: T0053364699N

Infrared preheating plate 1200 W,
230 V with Easy Fix board holder

KEY FEATURES

- + 1200 W, 230 V
- + Board size up to 190 x 245 mm
- + Temperature range 50 °C - 400 °C
- + Digital display for set and actual temperature
- + Digitally controlled
- + 6 Infrared high temperature ceramic elements for fast and efficient heat up
- + 2 Easy Fix board holder

TECHNICAL DATA

Height	70mm
Length	254mm
Dimensions L x W x H	254.0 x 395.0 x 70.0mm
ESD Safe	Yes
Heating Plate Dimensions	245.0 x 190mm
Interface	1 x RS232, 1 x Thermocouple Type K
Power	1200 W
Temperature Range (Depends on Tool)	50 - 400°C (150 - 750 °F)
Temperature Range °C	50 - 400 °C
Temperature Range °F	150 - 750 °F
Tip Type	WX
UPC	037103305459
Voltage	230V (50/60 Hz)
Product Family	Pre-Heating Plates