

T601 - PW3 Work Trousers

Collection: PW3

Range: Workwear

Shell Fabric: Titanmill Plus: 65% Polyester, 35% Cotton

Outer Carton: 15

Product information

The PW3 Work Trousers with its smooth lines and stylish cut offers superb working comfort. It offers an impressive range of pockets including double rule pocket and pre-shaped, top loading knee pad pockets. Premium features incorporate crotch gusset, hammer loop and reinforced panels for extra durability. With adjustable leg length for added convenience the Urban Trousers are the smart choice for the modern workplace.

PW3

Utilising premium fabrics, products are engineered for flexibility across a diverse range of industry and trade end uses and offer exceptional value.

Workwear

Portwest workwear offers a range of designs and features suitable for many end uses. Quality fabrics and construction techniques are used guaranteeing comfort and safety. Tested to withstand the rigours of everyday wear each garment has been carefully designed and manufactured to ensure optimum quality at the best price.

Standards

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)



Features

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reflective piping for increased visibility
- 10 pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Rule pocket
- 1 Spanner pocket
- 1 Pen pocket
- 1 Cargo pocket
- Top-loading knee pad pockets for quick and easy access
- 1 Hammer loop

T601 - PW3 Work Trousers

Commodity Code: 6203431100

Test House

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
T601BKR28	Black	65.0	45.0	36.0	0.8700	0.1053	5036108291397	25036108781564
T601BKR30	Black	65.0	45.0	36.0	0.8740	0.1053	5036108289820	25036108780048
T601BKR32	Black	65.0	45.0	36.0	0.9600	0.1053	5036108289837	25036108780055
T601BKR33	Black	65.0	45.0	36.0	0.9880	0.1053	5036108297436	25036108787191
T601BKR34	Black	65.0	45.0	36.0	0.9100	0.1053	5036108289844	25036108780062
T601BKR36	Black	65.0	45.0	36.0	0.9350	0.1053	5036108289851	25036108780079
T601BKR38	Black	65.0	45.0	36.0	0.9210	0.1053	5036108289868	25036108780086
T601BKR40	Black	65.0	45.0	36.0	1.0500	0.1053	5036108289875	25036108780093
T601BKR41	Black	65.0	45.0	36.0	0.9750	0.1053	5036108297443	25036108787207
T601BKR42	Black	65.0	45.0	36.0	0.9940	0.1053	5036108289882	25036108780109
T601BKR44	Black	65.0	45.0	36.0	1.0800	0.1053	5036108291403	25036108781571
T601BKR46	Black	65.0	45.0	36.0	1.0200	0.1053	5036108291410	25036108781588
T601BKR48	Black	65.0	45.0	36.0	1.1000	0.1053	5036108291427	25036108781595