

Hot air tool

HM 1820 S

Folding box
EAN 4007841 094003
Article number 094003



series 1



3 air volume levels



100 / 300 / 500 U/Min.



Suitable for pluggable nozzles



CE



VDE

Function description

All-rounder on 3 levels. The three-stage HM 1820 S hot air tool with three temperature settings: 50, 400 and 600°C. A real all-rounder for de-icing, drying, shaping, heat shrinking, paint stripping, soft-soldering and much more.

Technical specifications

Temperature	40 – 600 °C	Restart protection	No
Temperature setting	3-stage	Fine dust filter	No
Settings made via	multiple-stage switch	ESD	No
Airflow control	Settings	Cord length	2.2 m
Loc function	No	Dimensions (L x W x H)	253 x 85 x 200 mm
Motor, type	Brush motor	PU1, net weight	0,792 kg
Heating element	Micanite heating element	Manufacturer's Warranty	3 years
Function, hanger	Yes	PU1, EAN	4007841094003
Function, life expectancy, motor	600 h	Output	1300 W
Function, life expectancy, heating element	600 h	Product category	Hot air tool
Replaceable heating element	No		

Accessories

EAN 4007841 070311	Window nozzle 50 mm
EAN 4007841 070410	Window nozzle 75 mm
EAN 4007841 070113	Surface nozzle 50 mm

Hot air tool

HM 1820 S

Folding box
EAN 4007841 094003
Article number 094003



Accessories

EAN 4007841 070212	Surface nozzle 75 mm
EAN 4007841 070519	Reflector nozzle
EAN 4007841 010317	Paint Scraper Set
EAN 4007841 006648	Crimp connectors Ø 1,5 - 2,5 mm (10 ea.)