



ENGLISH

Datasheet

Stock No: 189-478

# RS Pro Plain Stainless Steel Pan Head Machine Screws



## Product Details


### Metric Thread, A4 Stainless Steel

A4 grade 18//8 stainless steel (Type 316 S16)

Higher level of corrosion resistance than A2 S/S

For use up to 300°C

Suitable for use in most food, medical, chemical, construction and electronic applications.



Pan Head Slotted Screws - Stainless Steel



ENGLISH

## Specifications:

Length	20mm
Thread Size Metric	M5
Head Shape	Pan
Material	Stainless Steel
Drive Type	Slot
Stainless Steel Type	A4, 316
Finish	Plain