



Main

| | |
|--------------------------------------|---|
| Range | Rilux |
| Product name | Rilux LED |
| Product or component type | Emergency light fitting |
| Function | Standard |
| Supply | Non-maintained |
| Light source | LED 0.3 W x 8 |
| Number of batteries | 1 x 3.6 V 1.5 Ah Ni-Cd (Nickel-Cadmium) |
| Wiring device additional information | Pictograms to be ordered separately |

Complementary

| | |
|--------------------------------|---|
| [Ue] rated operational voltage | 230 V 50 Hz |
| Power consumption in VA | 24 VA |
| Electrical insulation class | Class II |
| Autonomy | 1 h |
| Charging time | 12 h |
| Luminous flux | Emergency condition: 225 lm |
| Device mounting | Surface ceiling Flush false ceiling Wall mounted wall |
| Height | 51 mm |
| Width | 343 mm |
| Depth | 104 mm |
| Net weight | 0.59 kg |

Environment

| | |
|---------------------------------------|----------------------------|
| IP degree of protection | IP40 |
| IK degree of protection | IK06 |
| Ambient air temperature for operation | 0...40 °C |
| Fire resistance | 850 °C |
| Standards | EN 60598-2-22 IEC 50-11 |

Packing Units

| | |
|------------------------------|---------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Weight | 654 g |
| Package 1 Height | 5.1 cm |
| Package 1 width | 10.4 cm |
| Package 1 Length | 34.3 cm |

Offer Sustainability

| | |
|-------------------|---------------------|
| EU RoHS Directive | Under investigation |
|-------------------|---------------------|