

## Model 100 TH (Dual Scale)



NorTorque<sup>®</sup> utilises Norbar's proven mechanism and internal components and built them into a purposeful and attractive torque wrench.

In developing NorTorque<sup>®</sup>, Norbar's objective was to deliver outstanding quality and performance in a value for money package. Fine engineering ensures that the wrench adjustment is both fast and fingertip light meaning that you can do your job more efficiently.

Accurate to  $\pm 3\%$  of reading which meets and exceeds ISO6789 with models available to cover 12 N·m to 300 N·m.

**Part number:** 130142

**EAN Bar Code:** 5060207565554

**NATO number:** -

**Accuracy:**  $\pm 3\%$

**Operates between:**

**20.0 - 100.0 N·m**

**15.0 - 75.0 lbf·ft**



## TECHNICAL SPECIFICATIONS

- Length: 357mm
- Weight: 0.66kg
- End Fitting: 16mm Spigot

## FEATURES

- Convenient hanger feature for tool storage also aids wrench unlocking and adjustment
- Just eight turns to cover the entire scale
- Micrometer scale applying to the primary torque units (N·m on a dual scale wrench) for simple and error free setting
- Accurate to  $\pm 3\%$  of reading which meets and exceeds ISO6789
- Push/pull lock is fast and intuitive to use and prevents accidental adjustment of the set torque
- Light and fast adjustment saves operator time and effort
- Each tool is supplied with a traceable calibration certificate