



Figure similar

MLFB-Ordering data

6SL3210-5FE10-4UF0

Client order no. :

Item no. :

Order no. :

Consignment no. :

Offer no. :

Project :

Remarks :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V +10 % -15 %
Line frequency	45 ... 66 Hz

Output

Rated power	0.40 kW
Rated current (IN)	1.20 A
Max. output current	3.60 A

Inputs / outputs

Standard digital inputs

Number	4
--------	---

Digital outputs

Number	2
--------	---

Mechanical data

Degree of protection	IP20 / UL open type
Frame size	FSAA
Net weight	1.85 kg
Width	60.0 mm
Height	180.0 mm
Depth	200.0 mm

Ambient conditions

Cooling natural convection

Installation altitude 1000 m

Ambient temperature

Operation 0 ... 45 °C

Storage -40 ... 70 °C

Relative humidity

Max. operation 90 %

Standards

Compliance with standards CE, KC, cULus, EAC, C-Tick (RCM)

Communication

Communication PROFINET