

## Circuit Protection / Powerbreaker Portable RCD

### RCD PowerBreaker In line 16A 240V



#### Technical Specification

<b>Product Code</b>	J62-T
<b>Feature 1</b>	Suitable for BS or European power supply system
<b>Feature 2</b>	Robust Construction
<b>Feature 3</b>	Mechanical flag indicator
<b>Feature 4</b>	Double Pole Breaking
<b>Barcode</b>	5012739606441
<b>CE</b>	Y
<b>Colour</b>	Orange (Tangerine)
<b>Company DUNS Number</b>	216156018
<b>Country of Origin</b>	China
<b>Current (I)</b>	16
<b>Degree of Protection</b>	65

Tel No: 01279 772 772

Email: [sales@greenbrook.co.uk](mailto:sales@greenbrook.co.uk)

Website: [www.greenbrook.co.uk](http://www.greenbrook.co.uk)

<b>Finish body</b>	Gloss
<b>Fixings supplied with product</b>	None
<b>Frequency (Hz) max</b>	60
<b>Frequency (Hz) min</b>	50
<b>Greenbrook Guarantee (Years)</b>	1
<b>HS Code</b>	8536201090
<b>Ingress Protection (IP)</b>	IP65
<b>Installation method</b>	inline
<b>Latching</b>	Active
<b>Materials Main Body</b>	Polycarbonate
<b>Max Operating Current</b>	16
<b>Min Order Qty</b>	1
<b>Operating Temperature Range max C</b>	40
<b>Operating Temperature Range min C</b>	-5
<b>Package Product Max. Length (mm)</b>	180
<b>Package Product Max. Height (mm)</b>	85
<b>Package Product Max. Width (mm)</b>	102
<b>Package Product Weight gross (g)</b>	292
<b>Product (only) Max. Depth (mm)</b>	50.8
<b>Product (only) Max. Height (mm)</b>	161.5
<b>Product (only) Max. Width (mm)</b>	47
<b>Product Weight net (g)</b>	232
<b>RCD Contact Break</b>	Double pole
<b>RCD Type</b>	AC
<b>Sales Pack Qty</b>	1
<b>StatusCode</b>	Active
<b>UKCA</b>	Y
<b>Voltage (VAC) MAX (V)</b>	240
<b>Voltage (VAC) Min (V)</b>	220
<b>Voltage (VAC) Rated (V)</b>	230
<b>Wattage (W)</b>	3600
<b>Feature 5</b>	Separate test and reset button

Tel No: 01279 772 772

Email: [sales@greenbrook.co.uk](mailto:sales@greenbrook.co.uk)Website: [www.greenbrook.co.uk](http://www.greenbrook.co.uk)

