

## FEATURES

- Galvanised steel construction
- Easy to inspect for damage
- Shock absorbing
- High resistance to abrasion
- Fatigue rated at 1 – times the working load limit at 20 000 cycles

## RS PRO Eye Bolt M8

RS Stock No.: 124-4840



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

These Eye Bolts from our own RS PRO brand are intended for linear pulling loads in the direction of the thread. These Eye Bolts are proof tested and supplied complete with test certificate.

## General Specifications

|                           |                   |
|---------------------------|-------------------|
| <b>Type</b>               | Eye Bolt          |
| <b>Working Load Limit</b> | 0.14t             |
| <b>Material</b>           | Carbon Steel, C15 |
| <b>Finish</b>             | Zinc Plated       |

## Mechanical Specifications

|                             |                                  |
|-----------------------------|----------------------------------|
| <b>Diameter</b>             | 36mm                             |
| <b>Thread Size</b>          | M8                               |
| <b>Eye Outside Diameter</b> | 36mm                             |
| <b>Overall Height</b>       | 36mm                             |
| <b>Weight each</b>          | 0.052kg                          |
| <b>Applications</b>         | Tensioning Wires, Securing Loads |

## Safety Standard

|                      |              |
|----------------------|--------------|
| <b>Standards Met</b> | BS 4278:1984 |
|----------------------|--------------|

