

Rotary Hammer XGT®

HR005G

40Vmax • SDS-MAX • 40 mm • 8.0 J

Two-mode, anti-vibration rotary hammer for professionals

An efficient tool for SDS-MAX bits with AVT (anti-vibration technology) 40V max XGT batteries provide a high voltage. For impact and unstressed drilling and chipping. Speed range of 0 – 500 min⁻¹. Impact energy of 8.0 J, max. Capacity of 40 mm in concrete.



Technical specifications

Brushless Motor	✓
Nominal Battery Voltage	40 V
No load speed	250 - 500 min ⁻¹
Impacts per Minute (IPM)	1450 - 2900 min ⁻¹
Max. Drilling Diameter in Concrete	40 mm
Optimum Drilling Diameter Range in Concrete	16 - 35 mm
Impact Energy	8,0 J
Drilling diameter with TCT core bit	105 mm
Sound Power Level (L _{WA})	101 dB(A)
Sound Pressure Level (L _{pA})	90 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Chiselling	3,7 m/s ²
Tool weight with battery	7,4 - 8,8 kg
Product Dimensions (L x W x H):	500 x 115 x 286 mm

User benefits

- Soft start for smooth start-ups
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Brushless motor eliminates carbon brushes, enabling the Brushless motor to run cooler and more efficiently for longer life
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Optional AC

123138-5

Straight Side Handle

198993-4

Grease vessel for bit 100 ml

821837-0

Plastic Case

B-13845

Bull Point Chisel SDS-MAX 600 mm

B-13976

Clay Spade SDS-MAX, 135 x 400 mm

D-33978

T.C.T Drill Bit 20 x 200 / 340 mm,

D-33990

T.C.T Drill Bit 22 x 200 / 340 mm,

D-34017

T.C.T Drill Bit 24 x 200 / 340 mm,

D-34039

T.C.T Drill Bit 25 x 200 / 340 mm,

D-34051

T.C.T Drill Bit 28 x 250 / 370 mm,

D-34073

T.C.T Drill Bit 30 x 250 / 370 mm,

D-34095

T.C.T Drill Bit 32 x 250 / 370 mm,

D-34110

T.C.T Drill Bit 35 x 250 / 370 mm,

D-34132

T.C.T Drill Bit 38 x 250 / 370 mm,

D-34154

T.C.T Drill Bit 40 x 250 / 370 mm,

D-34176

Bull point SDS-MAX, 300 mm

D-34198

Bull point SDS-MAX, 600 mm



1914C5-7

Grease for SDS Drills & Hammers 30g



331955-1

Depth Gauge



B-13823

Bull Point Chisel SDS-MAX 280 mm



B-13873

Cold Chisel SDS-MAX, 25 x 600 mm



B-14021

Tile Chisel SDS-MAX 50 x 300 mm



D-33984

T.C.T Drill Bit 20 x 400 / 540 mm,



D-34001

T.C.T Drill Bit 22 x 400 / 540 mm,



D-34023

T.C.T Drill Bit 24 x 400 / 540 mm,



D-34045

T.C.T Drill Bit 25 x 400 / 540 mm,



D-34067

T.C.T Drill Bit 28 x 450 / 570 mm,



D-34089

T.C.T Drill Bit 30 x 450 / 570 mm,



D-34104

T.C.T Drill Bit 32 x 450 / 570 mm,



D-34126

T.C.T Drill Bit 35 x 450 / 570 mm,



D-34148

T.C.T Drill Bit 38 x 450 / 570 mm,



D-34160

T.C.T Drill Bit 40 x 450 / 570 mm,



D-34182

Bull point SDS-MAX, 400 mm



D-34207

Cold chisel SDS-MAX, 25 x 300 mm

Optional AC

D-34213

Cold chisel SDS-MAX, 25 x 400 mm



D-34229

Cold chisel SDS-MAX, 25 x 600 mm



D-34235

Scaling Chisel SDS-MAX 50 x 400



D-34241

Scaling Chisel SDS-MAX 80 x 300



Other

User manual

Parts drawing