



REV.	ECN NO.	DATE	SIGN	DESCRIPTION
C	LEN-030017~21	2010/03/02	Li Xiu Zhi	Delete mistaken View.
D	LEN1280080~84	2012/08/16	Ruru	Modify Note.
E	LEN1530265~69	2014/12/17	Ruru	Change Logo

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.



UA-20BFMM-SL7000 ①
Color: Black

UA-20BFMM-SL7AXX
 XX :01~05Meters
 01 :01Meter
 02 :02Meters
 ...
 05 :05Meters
 Cable Length(L):01~05Meters



Note:
 * @@Important Dimension.
 * Waterproof Rate:IP67.
 * Connector:Black,USB2.0-A Male Solder.
 * Cable:USB 2.0,28#*1P+24#*2C+Al/My+D+B, Black,PVC Jacket,UV Resistant,OD=5.0mm.
 * Cable Length Tolerance:01M:±40mm
 02M~05M:±60mm

Drain	28AWG	地線	Shield
Black	24AWG	黑	4
Green	28AWG	綠	3
White	28AWG	白	2
Red	24AWG	紅	1
Wire Color			Conn.
Pin Out			

Twist

UNIT:mm		TITLE USB, Cable Screw 20A F Conn M Pin	
TOLERANCE ±0.5 mm		SCALE Free	SHEET 1 OF 1
REV. E	SIZE A4	QC :Inspection Item	

Amphenol LTW
 安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY Ruru	DATE 2014/12/17
DWG NO UA-20BFMM-SL7AXX	CHECKED BY Rita	DATE 2014/12/17
CUSTOMER ALTW	APPROVED BY Win	DATE 2014/12/17