

Combination Hammer XGT®

HR007G

40Vmax • SDS-PLUS • 54 mm • 3,0 J

Three-mode, anti-vibration rotary hammer for professionals

HR007G has 3-mode operation; "rotation only", "hammering with rotation" and "hammering only". LED light illuminates drilling surface for more productivity in low light applications. It is also equipped with Auto-start Wireless System (AWS) and Anti-Vibration Technology (AVT).



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 980 min ⁻¹
Impacts per Minute (IPM)	0 - 5000 min ⁻¹
Max. Drilling Diameter in Wood	32 mm
Max. Drilling Diameter in Concrete	28 mm
Max. Drilling Diameter in Steel	13 mm
Optimum Drilling Diameter Range in Concrete	6 - 20 mm
Impact Energy	3,0 J
Drilling diameter with TCT core bit	54 mm
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	102 dB(A)

User benefits

- Soft grip handle provides increased comfort on the job
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Low power consumption thanks to brushless motor
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Brushless maintenance-free and long-life motor
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing