
## **KEMET Part Number: ALS30A472DE100**

(A331FH472M100A)



## ALS30, Aluminum Electrolytic, 4,700 uF, 20%, 100 VDC, -40/+85°C



Dimensions	
D	36mm +/-1mm
L	82mm +/-2mm
Т	7.14mm +/-0.5mm
S	12.8mm +/-0.5mm
DT	8mm +/-0.5mm
LT	87.5mm +/-1mm
TD	10mm MIN
V	8mm NOM

Packaging Specifications		
Weight:	115 g	
Sleeving:	Yes	
Packaging:	Bulk, Box	

General Information		
Supplier:	KEMET	
Series:	ALS30	
Dielectric:	Aluminum Electrolytic	
Description:	Screw Terminal, Aluminum Electrolytic	
RoHS:	Yes	
AEC-Q200:	No	
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M8x12. Mounting Clip (Sold Separately): V3/H2/UTE2736	
Shelf Life:	156 Weeks	

Specifications		
Capacitance:	4,700 uF	
Capacitance Tolerance:	20%	
Voltage DC:	100 VDC, 115 VDC (Surge)	
Temperature Range:	-40/+85°C	
Rated Temperature:	85°C	
Life:	11000 Hrs (Rated Voltage And Ripple Current At 85C), 22000 Hrs (Rated Voltage At 85C)	
Resistance:	33 mOhms (100Hz 20C), 27 mOhms (10kHz 20C)	
Ripple Current:	7.9 Amps (100Hz 85C), 8.8 Amps (10kHz 85C)	
Leakage Current:	2820 uA (5min 20°C)	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

