



LOGO! AM2 RTD EXPAN. MODULE,  
 PU: DC 12/24V, 2AI,  
 -50 ... +200 DEGR/C PT100/1000

Supply voltage	
12 V DC	Ja
24 V DC	Ja
Analog inputs	
Aantal analoge ingangen	2
Input ranges	
Uitvoering van de sensor / aan de analoge ingang / wordt ondersteund / sensor voor weerstandstemperatuur	Ja
EMC	
Emission of radio interference acc. to EN 55 011	
Emission of radio interference acc. to EN 55 011 (limit class B)	Ja
Degree and class of protection	
IP20	Ja
Standards, approvals, certificates	
Geschiktheidsbewijs / CSA-goedkeuring	Ja
UL approval	Ja
FM approval	Ja
developed in accordance with IEC 61131	Ja

<b>Marine approval</b>	
<b>Marine approval</b>	Ja
<b>Ambient conditions</b>	
<b>Operating temperature</b>	
<b>min.</b>	0 °C
<b>Omgevingstemperatuur / tijdens de werking / maximaal</b>	55 °C
<b>Dimensions</b>	
<b>Breedte</b>	36 mm
<b>Hoogte</b>	90 mm
<b>Diepte</b>	53 mm
Status	5-aug-2014