

NEW

slamer



PRODUCT CHARACTERISTICS



High resistance to heat and tearing



Non-magnetic



EVA sole for maximum comfort

S3 EN ISO 20345: 2011 SRC
HRO



HEEL REINFORCEMENT FOR MORE SUPPORT

■ 8824 BLACK | SIZE: 35 TO 48

COMPOSITION

Upper	Microfibre + Split leather
Lining	Fabric
Toe Cap	Composite
Stay clean insole	Mesh over PU foam. Removable. Anatomically shaped.
Puncture proof insert	Non-metallic
Sole	Rubber / EVA
Weight for size 42*	558g * Weight per shoe

SAFETY TABLE

	Toe cap (200J)
	Antipuncture sole
	Antislip sole **
	Shock-absorption
	Antistatic
	Oil and fuel resistant shoe
	Water-repellent upper

**

Size coefficient 42	Flat		Heel	
	Standard	Parade	Standard	Parade
SRA ceramic floor / Nals (soap solution)	0,32	0,44	0,28	0,40
SRB Steel / Glycerine (oil)	0,18	0,18	0,13	0,16