



Part Number : [731740083](#)
Product Description : 50 Ohms, BNC Plug
Straight, Crimp, RG-141, RG-303 and RG-58
Cable, One Piece Per Bag
Series Number : 73174
Status : Active
Product Category : RF / Coaxial Connectors




Documents & Resources

Drawings
[731740083_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73174
Description	50 Ohms, BNC Plug Straight, Crimp, RG-141, RG-303 and RG-58 Cable, One Piece Per Bag
Product Name	BNC
Style	Cable
Type	Miniature
UPC	800753691841

Electrical

Frequency	4 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	None
Net Weight	9.283/g
Orientation	Straight
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-141, RG-303, RG-58

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----
