



Main

Product or component type	Communication card
Range compatibility	Altivar 61 Altivar 71 Altivar 61Q Altivar 71Q
Communication port protocol	Profibus DP V1
Connector type	9-way female SUB-D connector
Transmission rate	1.5 Mbps 12 Mbps 187.5 kbps 19.2 kbps 3 Mbps 500 kbps 6 Mbps 93.75 kbps 9600 bps

Complementary

Number of addresses	1...126
Communication service	PPO type 8 PPO type 4 PPO type 3 PPO type 5 Communication monitoring can be inhibited, adjustable I/O data I/O profile CiA 402 profile
Display type	Graphic display terminal for reference received Graphic display terminal for I/O data Graphic display terminal for control word received 1 LED for ST (status) 1 LED for DX (data exchange)
Product weight	0.3 kg

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.