

Item code

TMAV 24.40



Brief description:

hoods for two levers, size "104.27" , top entry, M40, thermoplastic version, IP65

Product description		Approvals / Standards	
Version	T-TYPE insulating enclosures	Quality mark	 (type:12), EAC
Series	Hoods with 4 pegs	Conformity	CQC, CE
Product type	with 4 pegs	General ordering information	
Variant	top entry	EAN code	8015747168793
Family	T-TYPE insulating enclosures	Tariff number	85369095
Size	size "104.27"	Packaging Information	
Technical data		Packaging length	260,00 mm
Operating temperature range (min, max)	-40°C ... +90°C	Packaging height	210,00 mm
Material	thermoplastic	Packaging width	260,00 mm
IP degree of protection	IP65	Packaging weight	2,82 kg
Cable entry	M40	Packaging volume	14,20 dm ³
Other technical details		Packaging description	Carton box
Weight	141,00 g	Packaging quantity	20 Pcs
		Packaging EAN code	8015747171366
		Sub-packaging weight	0,71 kg
		Sub-packaging description	Plastic pakaging
		Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747171373

Item code

TMAV 24.40



Catalogue drawings

