

PREVOST FILTRATION - SINGLE UNITS

Filter-regulator



Part number	Female thread	Flow rate at 6.00 bar (l/min) ($\Delta P = 1.00$ bar)	Temperature min/ max (°C)	Max. operating pressure (bar)	Filtration (μm)	Net weight (Kg)
ATU M2585100	G1/8	700.00	5.00 / 50.00	10.00	25.00	0,463
ATU M2585101	G1/4	1000.00	5.00 / 50.00	10.00	25.00	0,463
ATU M2585102	G3/8	3000.00	5.00 / 50.00	10.00	25.00	0,9
ATU M2585103	G1/2	4500.00	5.00 / 50.00	10.00	25.00	0,9

