

Datasheet

## RS Pro Steel Alloy Compression Spring, 20.6mm x 2.82mm, 0.38N/mm

RS Stock No: **751-382**



### Product Details

RS Pro stainless steel alloy compression spring measures 20.6 x 2.82 mm and has a spring rate of 0.38 N/mm. It handles a load of 4.69 N at a minimum working length of 8.5 mm. This spring features right hand helix construction.

### Features and Benefits

- Wire diameter ends up to 0.8 mm are squared and ungrounded
- Wire diameter ends 1 mm and over are squared and ground
- Manufactured with a right hand helix



**Specifications:**

Ends	Closed (Square)/Unground
Material	Steel Alloy
Free Length	20.6 mm
Load at Minimum Working Length	4.69 N
Minimum Working Length	8.5 mm
Outside Diameter	2.82 mm
Spring Rate	0.38 N/mm
Wire Diameter	0.32 mm