

take care
cool your air



QuietSet Stand Fan HS1655E

Now comfortable can be quiet.

Elegant Stand fan with 5 cooling settings from whisper quiet up to turbo performance.



- ✓ QuietSet® control allows you to choose from 5 speeds/level of quiet control including sleep setting for ultra quiet operation
- ✓ Powerful, Quiet
- ✓ 1,2,4 or 8 hours auto shut-off timer
- ✓ Remote Control
- ✓ Adjustable Height
- ✓ Oscillation for wide area cooling
- ✓ Removable grille for easy cleaning
- ✓ No tool assembly

3 Year
Guarantee

take care
cool your air



Technical Information

EAN Codes

Retail Box- UK plug	HS-1655E1	04022167016553
Master Box- UK plug	HS-1655E1	14022167016550
Retail Box - EU plug	HS-1655E4	04022167416551
Master Box- EU plug	HS-1655E4	14022167416558
Input power	Watts	230V, 0.22A, 40W
Voltage/Frequency	V/~Hz	220-240V 50Hz
Speeds	5 speed settings	1-2-4-8 hour timer
Air flow capacity	approx. m/s.	3.5
Oscillation angle	degrees	110 degrees, tilt +/-7
Sound level	dB(A) / setting	<50 dB
Color		black/chrome
Dimensions of fan	L x W x H	55.0 x 17.0 x 58.0
Weight of fan	approx. kg	4.88
Dimensions of single box(cm)	L x W x H	55.0 x 17.0 x 58.5
Weight of single box	approx. kg	7
Master box quantity		2
Dimensions of master box	L x W x H	56.8 x 37.0 x 62.0
Weight of Master box	approx. kg	14.33
Pallet q.ty		16
Master box per layer		4
Number of layers		2

Specifications are subject to
change without notice
• HS-1655E June 2015

Honeywell is a trademark of Honeywell International Inc., used under license by Helen of Troy Limited.