



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #CAT-D9934-A15F
Header Assembly: Wire-to-Board, 5A, gold or tin plated




TE Part #6-1393030-5
SSRF-480D25R=SIP MDLE,25A, 480VAC,R-INT H

TE Part #2071385-2
OJE-SH-112HM2F,000



TE Part #2-1416010-6
RE034012



TE Part #2-1649329-2
RTE44012



TE Part #745286-3
LATCHING BLOCK SZ 1-4 BULK

TE Part #153265-E
USB MUSB-4V-P-HT 4 * * J 3 153899

TE Part #1-1721260-1
OJ-SH-112LMH2



TE Part #133209-E
MJ HS G * 8 8 4B * GF5 * * 30 * J 3 1339

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_2-1423008-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1423008-1_F.3d_stp.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1423008-1_F.3d_igs.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

T92 Two-Pole, 30 Amp, PC Board or Panel Mount Relay

English

Product Specifications



T92 TRAY PACKING

English

Definitions General Purpose Relays

English

Agency Approvals

CQC_CERT_16002142754_C1

English