6 Gauge Minimess® Pressure Test Kit

Features

- New addition to our popular **Minimess® pressure test kit series** with up to 6x selectable pressure gauges and 5x Minimess® 1620 test points.
- Robust multi-gauge measuring kit for rapid pressure testing of all hydraulic system pressures.
- Test under pressure using leak free Minimess® connections up to 630 bar.
- Tool free Minimess® connection for quick, safe and easy pressure measurement.
- Ideal for the mobile hydraulic, construction and agricultural service engineers.

RS PRO 6 Gauge Minimess® Pressure Test Kit

RS Stock No.: 0848938



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.


6 Gauge Minimess® Pressure Test Kit


Technical Specifications

- 6 x 63mm glycerine fi lled pressure gauges 0...40 bar, 70 bar, 100 bar, 160 bar, 280 bar and 400 bar. All fitted with Minimess® 1620 male hose connectors.
- 5 x Minimess® test points - 1/8" & 1/4" BSP, M10x1, 1/4" NPT & 9/16"-18 UNF male threaded.
- 3 x 630 bar rated Minimess® 1620 pressure test hoses - 1.5 meters long.



Box dimensions: (400 x 300 x 120 mm)





6 Gauge Minimess® Pressure Test Kit

Kit Contents



1. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...40 bar pressure range).
2. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...70 bar pressure range).
3. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...100 bar pressure range).
4. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...170 bar pressure range).
5. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...280 bar pressure range).
6. 63mm analogue pressure gauge with Minimess® 1620 male connection (0...400 bar pressure range).
7. Minimess® 1620 test point. 1/4" BSP male.
8. Minimess® 1620 test point. 1/8" BSP male.
9. Minimess® 1620 test point. 9/16" UNF male.
10. Minimess® 1620 test point. 1/4" NPT male.
11. Minimess® 1620 test point. M10x1 male.
12. Minimess® 1620 test hoses 1.5m long. 630 bar max working pressure (x3).