

## Metal drill bits HSS PointTeQ, with reduced shank

- ▶ Twist drill bit made of high-speed steel
- ▶ Right-hand cutting twist drill bit, Type N, 135° from 4 mm upwards (below 118°)
- ▶ Shank is reduced to 10 mm for drill bits with diameter ≤13 mm and to 12 mm for drill bits with diameter >13 mm
- ▶ Two-cutter, cylindrical, two flutes



PRODUCT PROPERTIES				ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
Pack of 1								
10.5	87	133	10	PC1d	1	5	3165140908085	2 608 577 299
11	94	142	10	PC1d	1	5	3165140908092	2 608 577 300
11.5	94	142	10	PC1d	1	5	3165140908108	2 608 577 301
12	101	151	10	PC1d	1	1	3165140908115	2 608 577 302
12.5	101	151	10	PC1d	1	1	3165140908122	2 608 577 303
13	101	151	10	PC1d	1	1	3165140908139	2 608 577 304
13.5	108	160	12	PC1d	1	1	3165140908146	2 608 577 305
14	108	160	12	PC1d	1	1	3165140908153	2 608 577 306
14.5	114	169	12	P1c	1	1	3165140908160	2 608 577 307
15	114	169	12	P1c	1	1	3165140908177	2 608 577 308
15.5	120	178	12	P1c	1	1	3165140908184	2 608 577 309
16	120	178	12	P1c	1	1	3165140908191	2 608 577 310
16.5	125	184	12	P1c	1	1	3165140908207	2 608 577 311
17	125	184	12	P1c	1	1	3165140908214	2 608 577 312
18	130	191	12	P1c	1	1	3165140908221	2 608 577 313
19	135	198	12	P1c	1	1	3165140908238	2 608 577 314
20	140	205	12	P1c	1	1	3165140908245	2 608 577 315