

VARTA Recharge Accu Power AAA 800 mAh Piece



VARTA Recharge Accu Power: The most powerful product line offering best battery performance.



Information

- Pre-charged and with 'ready to use' technology - for immediate usage straight from the pack
- Rechargeable hundreds of times without memory effect
- Suitable for all standard and smart devices of daily use and all NiMH chargers
- Best use in high drain applications and devices with constant energy requirements like LED flashlights, GPS systems, wireless mice and more
- Lasts up to 8 times longer in digital cameras*
- * vs. VARTA Energy. Based on IEC 60086-2 (ed. 14.0) DSC-Test for FR10G445. May vary by device.

Article Details

Ordernumber	56703 101 111
Customs Tariff Number	85075000
Country Of Origin	China
IEC	HR03
Others	56703, AAA, Ministilo
Nominal Capacity	800 mAh
Voltage	1.20
System	Nickel Hydride
Consumer Unit	1
DG Profile	NiMH battery UN3496 (sea to 100kg ok)

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 550852				0.01
SK2 (Inner carton 2)	10	40 08496 550869	56.00	23.00	45.00	0.14
SK1 (Inner carton 1)	40	40 08496 550876	95.00	60.00	50.00	0.56
VSK (Master carton)	360	40 08496 550883	188.00	162.00	110.00	5.16
PAL (Pallet)	65520	40 08496 550890	800.00	1,200.00	920.00	960.48

Layer / Pallet	Master carton / Layer	Master carton / Pallet	Minimum pieces / shipment unit
7	26	182	10

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.

VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
 P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

