

Datasheet

RS Pro Right Angle Cable Mount SMC Connector, Plug, Clamp Termination, RG174 A/U

RS Stock No: **546-3434**



Product Details

RS Pro cable mount SMC connector plug includes soldered centre contact. This right angle connector plug comes with a solder-cable clamp termination. It is compatible with RG174 A/U cable type.

Features and Benefits

- Gold plated
- Suitable for use with RG174 cable
- Centre contact is soldered

Specifications:

Body Orientation	Right Angle
Body Plating	Gold
Cable Type	RG174 A/U
Contact Material	Beryllium Copper
Contact Plating	Gold
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Operating Frequency	10 GHz
Size	Subminiature
Termination Method	Clamp
Dimensions	14 x 12.8 mm
Operating Temperature Range	-65 to +165°C