



ENGLISH

Datasheet

RS Pro 3W Surface & Recessed Downlight

RS Stock No: 189-6586



This RS Pro Surface & Recessed Downlight is suitable for use in both Industrial and commercial applications, such as hospitals, factories, leisure facilities, schools and hotels. This Fitting is supplied non-maintained with 3 interchangeable optical lenses. This fitting can be surface and recessed mounted.



Typical Properties

ENGLISH

Material	Polycarbonate
Wattage	3W
Supply Voltage	220 – 240 50Hz
Battery	3.6V 1700mAh Ni-Cad
Colour Temperature	6000k
Light Colour	Daylight
Lumens	140 Lm
Emergency Duration	Minimum 3 hours
Indicators	Green, battery charge
Product Colour	White
Lens Interchangeable	Yes
Dimmable	No
IP Rating	IP20
Rated Life	35,000 Hours
Warranty	3 Years

